

Diaphragm seals for sanitary use

Model DS205

Standard Tri-clamp connections
ASME B40.100

Features

- SS 316L diaphragms welded to a SS316L top housing
- Compatible with Tri-Clover
- Easy to remove from process

Ranges

15 psi up to 1600 psi
1 kg/cm² up to 40 bar & kg/cm²
100 kPa up to 4000 kPa

Applications


Pharmaceuticals
Dairy & Food process industry
Biotechnology and filtration industries
Breweries, distilleries, wineries and citrus juice production plants

2
YEARS
WARRANTY



Model	DS205	
Process connection size	1 1/2" Clamp	2" Clamp
Pressure range in bar (min max)	0/2.5 0/40 for 63mm (2.5"), 0/4 0/40 for 100mm (4")	0/1 0/40 for 63mm and 100mm (4")
Instrument Connection	1/4" BSP (F)	
Material, Diaphragm & Top housing	Stainless steel 316L	
Accuracy	Additional 0.5 % to the specified tolerance of the mounted instrument	
Filling liquids (temperature range)	Glycerin (0/300 °F, -18/150 °C), vegetable oil (32/248 °F, 0/120 °C), Food grade silicone (-13/400 °F, -25/200 °C)	
Mounting	Direct	
Weight in grams	160	240
Accessories, options	Pressure gauges, transducer	

General dimensions in mm



1 1/2" Tri-clamp

2" Tri-clamp

Order information

Process connection	Type	Diaphragm and top housing	Instrument connection	Filling fluid	Options
(15) 1 1/2" Tri-clamp (20) 2" Tri-clamp	DS205	(S) 316L	(13T) 1/4" BSP(F)	(CG) Glycerin (direct mounted, -18/150 °C) (GZ) Vegetable oil (direct mounted, 0/120 °C) (CZ) Food grade silicone (direct mounted or with capillary, -25/200 °C) others on request	(NH) Tagging marked (C) Clamp (G) Gasket (PE) Electro polishing

How to order

Process connection	Type	Diaphragm and top housing	Instrument connection	Filling fluid	Option
15	DS205	S	13T	GZ	NH